

#### **GEM DPSS CONTINUOUS WAVE LASER SERIES**

# COMPACT AND RELIABLE WITH HIGH SPECIFICATIONS

Novanta develops photonics solutions specializing in cutting-edge components and sub-systems for laser-based diagnostic, analytical, micromachining and fine material processing applications. Powerful lasers, coupled with advanced beam steering and intelligent sub-systems incorporating software and controls, deliver extreme precision and performance, tailored to our customers' demanding applications.

#### **BUILT FOR OEMS**

The gem range is the OEM laser of choice. Designed of easy integration into OEM instrumentation the gem series incorporates high output power from a compact platform, exceptional wall plug efficiency for effective thermal management and robust optomechanical design to support high reliability, 24/7 system integrated applications. Advanced design features including an integrated power feedback for exceptional power and spectral stability and fiber coupling solutions will benefit a range of applications from Super Resolution Microscopy, Raman Spectroscopy and Hologram Replication through to Semiconductor inspection and Particle Counting.





The gem laser available in a range of wavelengths and powers

#### **UNIQUE FEATURES**

#### **OEM focused platform**

- Flexible, customizable platform to meet exact OEM integrator requirements.
- Advanced features including high power SM and MM fiber coupling solutions and high power/footprint ratio.
- Robust optomechanical design for prolonged longevity and minimized downtime

### Exceptional performance supporting consistent and repeatable results.

- Exceptional power stability and low noise for high repeatability, resolution and consistency in a diverse array of application
- High power on sample via either free space or fiber delivery.

#### Ease of integration

- High wall-plug efficiency for effective thermal management Air cooled solutions.
- Simple plug and play solution increasing productivity and allowing for field replacements.
- Compact laser head and psu; easy to design in new or retrofit in existing OEM instruments.

#### **GEM DPSS CONTINUOUS WAVE LASER SERIES**

#### PERFORMANCE DATA

The gem range is a series of compact lasers designed for easy OEM integration. With a wide power range and multiple wavelength offerings, the gem is ideal for system designers requiring a reliable, robust laser with excellent beam quality. All gem lasers are high specification single transverse mode CW lasers, ideal for many applications such as Raman and super-resolution microscopy. The gem range has a long industrial heritage, delivering extended performance lifetimes that truly enable it to be treated as a black box to be installed and forgotten (Fig. 1).




Fig. 1 Output power from 4 gem lasers, showing stable output over 45,000 hours, with minimal increase in required diode current.




Fig. 2 Accelerometer trace showing the 1200 g shock experienced by all Laser Quantum lasers prior to testing.

#### FLEXIBLE DESIGN

Customizable options available for your laser to optimize your application.

- Fiber coupling: Available with multi or single mode fiber delivery options which allows the beam to be delivered to the point of need.
- Intelligent control unit: Allows easy setting and monitoring of the laser parameters. Incorporating PowerLoQ™ technology, the gem lasers show extreme power stability over long periods of use.
- 1200 g drop-test: (Fig. 2) All gem lasers undergo a drop test to check that all components are correctly fitted prior to its extended 300 hour test period. This rigorous testing regime ensures long operational lifetimes.
- RemoteApp™: Works with software that allows the laser to be controlled locally, over the internet and connected directly to our support team for monitoring laser performance, diagnosing opportunities and carrying out laser optimization.
- Available in a range of wavelengths and powers: The gem
  family of lasers are designed for integration into instruments as
  a fit-and-forget laser source, with exceptionally long operation
  lifetimes.

#### **GEM DPSS CONTINUOUS WAVE LASER SERIES SPECIFICATIONS**

| Specification                        | gem 532           | gem 561        | gem 640        | gem 660        | gem 671        |
|--------------------------------------|-------------------|----------------|----------------|----------------|----------------|
| Wavelength                           | 532 nm            | 561 nm         | 640 nm         | 660 nm         | 671 nm         |
| Power                                | 100 - 2000 mW     | 100 - 1000 mW  | 100 - 500 mW   | 100 - 1000 mW  | 100 - 750 mW   |
| Beam Diameter <sup>1</sup>           | 0.9 ± 0.1 mm      | 1.0 ± 0.2 mm   | 1.1 ± 0.2 mm   | 0.75 ± 0.15 mm | 0.75 ± 0.15 mm |
| Spatial Mode                         | TEM <sub>oo</sub> |                |                |                |                |
| Ellipticity                          | < 1:1.2           |                |                |                |                |
| Bandwidth                            | 30 GHz            | 40 GHz         | 40 GHz         | 30 GHz         | 30 GHz         |
| Divergence                           | < 0.8 mrad        | < 1 mrad       | < 1.2 mrad     | < 1.5 mrad     | < 1.5 mrad     |
| M <sup>2</sup>                       | < 1.1             | < 1.2          | < 1.2          | < 1.2          | < 1.2          |
| Power Stability (RMS) <sup>2</sup>   | < 0.8%            | < 1.0%         | < 0.8%         | < 1.0%         | < 1.0%         |
| Noise (RMS)                          | < 0.8%            | < 1.5%         | < 0.8%         | < 0.6%         | < 0.6%         |
| Noise Bandwidth                      | 10 Hz - 6 MHz     | 10 Hz - 10 kHz |
| Beam Pointing Stability <sup>3</sup> | <10 µad/°C        |                |                |                |                |
| Polarization Ratio                   | > 100:1           |                |                |                |                |
| Polarization Direction <sup>4</sup>  | Horizontal        |                |                |                |                |
| Coherence Length                     | ~1 cm             | ~7.5 mm        | -~7.5 mm       | ~1 cm          | ~1 cm          |
| Beam Angle <sup>5</sup>              | <1 mrad           |                |                |                |                |
| Operating Temperature                | 15 - 40° C        | 15 - 40° C     | 22 - 37° C     | 15 - 40° C     | 15 - 40° C     |
| Standard Power Supply Unit           | smd12             | smd12          | smd24          | smd12          | smd12          |

 $<sup>{}^{\</sup>star} \textit{Laser Quantum operates a continuous improvement programme which can result in specifications being improved without notice.}$ 

 $<sup>1\,</sup>Beam\,diameter\,defined\,as\,the\,average\,of\,major\,and\,minor\,1/e^2\,beam\,size\,measured\,at\,25\,cm\,from\,exit\,port,\,at\,specified\,power.$ 

<sup>2</sup> Test duration >100 hrs. at constant temperature.


<sup>3</sup> Measured over 36 hrs. at 22 to 28 °C.

<sup>4</sup> Vertical polarization is available upon request.

<sup>5</sup> Tolerance relative to head orientation.

#### **GEM DPSS CONTINUOUS WAVE LASER SERIES**

#### **DIMENSIONS (mm)**






Drawings are for illustrative purposes only, please contact us for complete engineer's drawings

#### ADDITIONAL INFORMATION


Customizable options available for your laser to optimize your application.

- Weight: 0.75 kg
- Weight: 0.8 kg (gem 640 only)
- Umbilical length: 1.5 m
- Cooling options available
- System can be modulated
- Vertical polarization is available on request
- Fiber coupling available
- LabView drivers available
- 2 years unlimited hours warranty for scientific users

#### SMD24 POWER SUPPLY UNIT



#### SMD12 POWER SUPPLY UNIT



#### **CONTACT US**

#### Americas, Asia Pacific

Novanta Headquarters Bedford, USA P +1-781-266-5700

Photonics@Novanta.com

#### Europe, Middle East, Africa

Novanta Europe GmbH Wackersdorf, Germany P +49 9431 7984-0

Milan, Italy P+39-039-793-710

Photonics@Novanta.com

#### China

Novanta Sales & Service Office Shenzhen, China P +86-755-8280-5395

Suzhou, China P +86-512-6283-7080

Photonics.China@Novanta.com

#### Japan

Novanta Service & Sales Office Tokyo, Japan P +81-3-5753-2460

Photonics.Japan@Novanta.com

## 光と人をつなぐ

# Rayture Systems



レイチャーシステムズ株式会社

〒160-0006 東京都新宿区舟町7 ロクサンビル7 F

TEL: 03-3351-0717 FAX: 03-3351-6771

URL: <a href="http://www.rayture-sys.co.jp">http://www.rayture-sys.co.jp</a>

E-mail: laser@rayture-sys.co.jp