

RX2 Series Picosecond Lasers

www.photonix.com

Photonics Industries' RX2 Series mid power picosecond lasers offer high performance, high precision, and robust form factor for the most demanding industrial as well as scientific applications. Photonics Industries is proven, with over a thousand picosecond lasers shipped worldwide, to meet and fulfill precision needs in manufacturing, scientific research, and new, emerging requirements necessitating ever smaller pulse widths in the ultrafast regime.



Applications

- Cutting/Drilling/Scribing Thin Metal/Metal Foil, Ceramic, Glass, Ultra Thin Glass (UTG), Plastic, Glass-reinforced Plastic
- Flat Panel Display, LCD/LED/OLED Repair/Microprocessing
- Ink-Jet Nozzle Hole Drilling, Laser Milling Ink-Jet Nozzle Holes, Laser Ablation Ink-Jet Nozzle Holes
- Brittle Material Microprocessing
- Medical Stents, Medical Device Laser Microprocessing
- Low-k Dielectric Wafers, Silicon Wafers, Flexible Printed Circuit Boards (FPCB), Printed Circuit Boards (PCB) Microprocessing
- Hydrophobic Material Manufacturing, Hydrophilic Material Manufacturing, Ultrafast Laser Assisted Etching (ULAE) Systems

Features

High single pulse energy:
 Up to ~600 μJ, RX2 IR models

Short pulse laser:

~10 ps for IR, ~7 ps for Green & UV Option up to ~30 ps available

Wide range of wavelengths:

1064 nm, 532 nm, 355 nm

MWB, MWS, & 266 nm options on request

 Smallest, all-in-one (AIO), high power picosecond laser on the market:

Up to 100 W IR, 70 W GRN, or 28 W UV

- Highest efficiency picosecond laser with the lowest power consumption:
 - < 700 W typical
- High repetition rates:

Options up to 15 MHz or ~32 MHz

Excellent TEM00 beam, and Pointing Stability:

Typical $M^2 < 1.2$; < 20 µrad

• Exceptional and Versatile Pulse Control:

PEC (Power or Pulse Energy Control).

PSO (Position Synchronized Output) mode for external triggering to any arbitrary PRF while maintaining a constant, stable pulse energy with low jitter.

Burst Mode for individually controllable pulses in burst envelopes of up to 10 pulses with intra-burst pulse separation of ~ 31 ns.


POD (Pulse-On-Demand) pulse bursts can be triggered internally, externally, or continuously, while maintaining constant pulse energy.

	RX2-1064-60	RX2-1064-100
Beam and output specificat	tions	
Wavelength [⊕]	1064 nm	
Output power ¹	60 W	100 W
Long term power stability ²	≤ 1% rms	
Pulse width [⊕]	~10 ps	
Pulse repetition rate ^{3,⊕}	Single shot to 2 MHz (option up to 15 MHz)	
Pulse-to-pulse stability ⁴	~1% rms	
Beam diameter, at exit	~2 mm	
Beam spatial mode	TEM ₀₀ M ² ~1.2	
Beam pointing stability	< 20 μrad	
Beam divergence	< 2 mrad	
Beam roundness	> 90%	
Beam bore sight accuracy	\leq 1 mm lateral (to specified exit location), \leq 5 mrad angular (to specified exit direction)	
Polarization	Vertical >100:1	
Operational specifications a	and system characteristics	
Interface	RS232, Ethernet, Software GUI, External TTL Triggering	
Warm-up time	< 15 minutes	
Electrical requirement	100-240 V AC; or 32 V DC, 15 A	
Line frequency	50-60 Hz	
Climate	Ambient 15°C to 30°C (59°F to 86°F) Operating Range,	
	Relative Humidity 90% Maximum, non-condensing	
Power consumption ⁵	< 700 W	
Dimensions (LxWxH) ⁶	21 x 10 x 3.75 in.	
Weight	~70 lbs	
Vibrational tolerance	Up to 3g	
Cooling system	Closed-loop chiller	

⊕ See options in below table.

[1.] Output power is specifiable at different pulse repetition rates for optimal pulse energy. [2.] Measured over 8 hours ± 1°C. [3.] Lower repetition rates, down to single shot, achieved by utilizing PSO or POD features. [4.] Measured at ambient temperature ± 2°C. [5.] Power consumption data does not include an external chiller's power consumption. [6.] RX Series picosecond lasers are all-in-one (AIO) and do not require a separate controller or utility module. All connections for operation and control of the laser can be found on the back panel of the AIO laser.

Options	Designation
Pulse width ~30 ps,	-LP
Long pulse option	e.g., RX2-1064-80-LP
Single shot to 15 MHz,	-15M
High pulse repetition rate option	e.g., RX2-1064-60-15M
Fixed pulse repetition rate ~32 MHz,	-QCW
Quasi-CW (continuous-wave) operation option	e.g., RX2-1064-80-QCW
Multi-wavelength blended or selectable output option	-MWB, or -MWS
	e.g., RX2-1064-100-MWB





	RX2-532-40	RX2-532-70	
Beam and output specifications			
Wavelength [⊕]	532 nm		
Output power ¹	40 W	70 W	
Long term power stability ²	≤ 1% rms		
Pulse width [⊕]	~7 ps		
Pulse repetition rate ^{3,⊕}	Single shot to 2 MHz (option up to 15 MHz)		
Pulse-to-pulse stability ⁴	< 2% rms		
Beam diameter, at exit	~1 mm		
Beam spatial mode	$TEM_{00} M^2 < 1.2$		
Beam pointing stability	< 20 μrad		
Beam divergence	≤ 1 mrad		
Beam roundness	> 90%		
Beam bore sight accuracy	≤ 1 mm lateral (to specified exit location), ≤ 5 mrad angular (to specified exit direction)		
Polarization	Horizontal >100:1		
Operational specifications a	and system characteristics		
Interface	RS232, Ethernet, Software GUI, External TTL Triggering		
Warm-up time	< 15 minutes		
Electrical requirement	100-240 V AC; or 32 V DC, 15 A		
Line frequency	50-60 Hz		
Climate	Ambient 15°C to 30°C (59°F to 86°F) Operating Range,		
	Relative Humidity 90% Maximum, non-condensing		
Power consumption ⁵	< 700 W		
Dimensions (LxWxH) ⁶	21 x 10 x 3.75 in.		
Weight	~70 lbs		
Vibrational tolerance	Up to 3g		
Cooling system	Closed-loop chiller		

Cooling systemSee options in below table.

① See options in below table.

[1.] Output power is specifiable at different pulse repetition rates for optimal pulse energy. [2.] Measured over 8 hours ± 1°C. [3.] Lower repetition rates, down to single shot, achieved by utilizing PSO or POD features. [4.] Measured at ambient temperature ± 2°C. [5.] Power consumption data does not include an external chiller's power consumption. [6.] RX Series picosecond lasers are all-in-one (AIO) and do not require a separate controller or utility module. All connections for operation and control of the laser can be found on the back panel of the AIO laser.

Options	Designation
Pulse width ~20 ps,	-LP
Long pulse option	e.g., RX2-532-35-LP
Single shot to 15 MHz,	-15M
High pulse repetition rate option	e.g., RX2-532-50-15M
Fixed pulse repetition rate ~32 MHz,	-QCW
Quasi-CW (continuous-wave) operation option	e.g., RX2-532-35-M-QCW
Multi-wavelength blended or selectable output option	-MWB, or -MWS
	e.g., RX1-1064-10-MWB



	RX2-355-20	RX2-355-28		
Beam and output specifications				
Wavelength [⊕]	355 nm			
Output power ¹	20 W	28 W		
Long term power stability ²	≤ 1% rms			
Pulse width [⊕]	~7	~7 ps		
Pulse repetition rate ^{3,⊕}	Single shot to 2 MHz (option up to 15 MHz)			
Pulse-to-pulse stability ⁴	~2% rms			
Beam diameter, at exit	~4 mm			
Beam spatial mode	$TEM_{00} M^2 < 1.2$			
Beam pointing stability	< 25 μrad			
Beam divergence	≤ 1 mrad			
Beam roundness	> 90%			
Beam bore sight accuracy	≤ 1 mm lateral (to specified exit location), ≤ 5 mrad angular (to specified exit direction)			
Polarization	Vertical >100:1			
Operational specifications	and system characteristics			
Interface	RS232, Ethernet, Software GUI, External TTL Triggering			
Warm-up time	< 15 minutes			
Electrical requirement	100-240 V AC; or 32 V DC, 15 A			
Line frequency	50-60 Hz			
Climate	Ambient 15°C to 30°C (59°F to 86°F) Operating Range,			
	Relative Humidity 90% Maximum, non-condensing			
Power consumption ⁵	< 700 W			
Dimensions (LxWxH) ⁶	$25.5 \times 10 \times 3.75$ in.			
Weight	~70 lbs			
Vibrational tolerance	Up to 3g			
Cooling system	Closed-loop chiller			


[⊕] See options in below table.


① See options in below table.


[1.] Output power is specifiable at different pulse repetition rates for optimal pulse energy. [2.] Measured over 8 hours ± 1°C. [3.] Lower repetition rates, down to single shot, achieved by utilizing PSO or POD features. [4.] Measured at ambient temperature ± 2°C. [5.] Power consumption data does not include an external chiller's power consumption. [6.] RX Series picosecond lasers are all-in-one (AIO) and do not require a separate controller or utility module. All connections for operation and control of the laser can be found on the back panel of the AIO laser.

Options	Designation
Pulse width ~20 ps,	-LP
Long pulse option	e.g., RX2-355-20-LP
Single shot to 15 MHz,	-15M
High pulse repetition rate option	e.g., RX2-355-40-L-15M
Fixed pulse repetition rate ~32 MHz,	-QCW
Quasi-CW (continuous-wave) operation option	e.g., RX2-355-40-M-QCW
Multi-wavelength blended or selectable output option	-MWB, or -MWS
	e.g., RX1-1064-10-MWB










Dimensional Drawing



Copyright © 2023 by Photonics Industries International, Inc.

Main Headquarters: 1800 Ocean Ave, Ronkonkoma, New York 11779, United States

<u>Photonics Industries International</u> is the pioneer of <u>intracavity harmonic lasers</u> and is at the forefront of developing, manufacturing and marketing a wide range of nanosecond, sub-nanosecond, picosecond and femtosecond lasers for industrial, scientific, defense, and medical industries. Check out our <u>products</u> and see how we can help you <u>apply</u> our lasers to your needs.





光と人をつなぐ

Rayture Systems



レイチャーシステムズ株式会社

〒160-0006 東京都新宿区舟町7 ロクサンビル7 F

TEL: 03-3351-0717 FAX: 03-3351-6771

URL : http://www.rayture-sys.co.jp

E-mail: laser@rayture-sys.co.jp